

ML_8200REC Recessed Baby Change Station

Note

This product is to be installed by suitably qualified persons, in a fit-for-purpose application, to suitable materials, using suitable fixings, and complying with any relevant codes.

Dimensions


- **Open:** 940mmW x 585mmH x 495mmD
- **Closed:** 940mmW x 585mmH x 14mmD
- **Wall Opening:** 905mmW x 530mmH x 92mmD

Hardware Provided

- 4x Slotted Hex Head Screws (For Side Fixing)
- 4x Wall Plugs (For Side Fixing)
- 4x Shoulder Washers (For Side Fixing)
- 5x Sleeve Anchors (For Rear Fixing)

Before Installation

- Inspect the product. If there is any damage or missing parts, do not install the product and contact your place of purchase.
- Ensure the surface you wish to mount the station in is either solid or has adequate in-wall support.
- Ensure the surface you wish to mount the station in is flat.
- Check that there will be adequate clearance for the station to be folded open once installed.



This product is accessible compliant when installed in accordance with AS 1428.1 guidelines.

The photographs and line drawings of the products presented above are representational only. Metlam Australia Pty Ltd reserves the right to, and from time to time, make changes and improvements in design and dimensions.

Installation Instructions

Placement may be subject to regulations/codes and architectural drawings. Correct positioning is the responsibility of the installer.


1. Create a rough wall opening 905mm Wide x 530mm High.
2. Mark the four side mounting holes on the noggin, checking that all sides are level. If preferred/possible, the five rear mounting holes can be used.
3. Install suitable fasteners at the marked locations and mount the station.
4. Apply neutral cure silicone to all edges where the station meets the wall.
5. Test station for correct operation.

Note Regarding Accessible Compliance:

"Where installed, baby change tables shall ... have a maximum height of 820 mm and a minimum clearance of 720 mm when in the open position"

- AS 1428.1:2021 clause 12.2.8.2

Rear fixing mounting template:



Technical recommendations and installation advice from Metlam Australia Pty Ltd are general in nature and provided in good faith without warranty. Metlam disclaims all liability for errors, omissions, or damage resulting from improper installation or maintenance. All products must be installed by qualified tradespeople and maintained by competent personnel. It is the installer's responsibility to conduct thorough pre-installation assessments; Metlam Australia will not enter into post-installation disputes regarding positioning, functionality, or external factors affecting performance.

The photographs and line drawings of the products presented above are representational only.
Metlam Australia Pty Ltd reserves the right to, and from time to time, make changes and improvements in design and dimensions.